



SP62

PORTABLE SPHERE SPECTROPHOTOMETER

ADVANCED
COLOR
MEASUREMENT

—in the laboratory, plant or field

- Lightweight, compact, portable instrument
- Diffuse/8° sphere optical geometry
- 0.15 ΔE_{cmc} inter-instrument agreement
- 4mm, 8mm or 14mm measurement areas
- Large, easy-to-read graphical LCD display
- PROJECT operation mode
- Flip-back target shoe for flexible use
- Simultaneous measurement of both specular component included and specular component excluded
- Rugged construction
- Rechargeable battery for remote use



EXPERIENCE

the measurable color difference.™

SP62

PORTABLE SPHERE SPECTROPHOTOMETER

The SP62 is a versatile sphere spectrophotometer, designed to give fast, precise and accurate color measurement information on materials ranging from paper and paint to plastics and textiles.

Measuring Functions and Indices

The SP62 provides absolute and difference measurements for the following colorimetric systems. These values can be obtained for any of nine illuminants with 2° or 10° observer angle: CIE XYZ, CIE Yxy, CIE L*a*b*, Hunter Lab, CIE L*c*h°, CMC and CIE94. Whiteness and Yellowness per ASTM E313-98, Metamerism Index and DIN 6172 + AATCC Gray Scale.

Special PROJECT Modes

Multiple color standards can also be collected under an identified PROJECT, a feature that supports corporate color standards programs.

Pass/Fail Mode

The SP62 stores up to 1,024 standards with tolerances for easy pass/fail measurement. A red/green LED-illuminated indicator and the LCD display provide visual confirmation of results. A tone also sounds to indicate a fail result.

Quick Color Compare

An operator can take a quick measurement and comparison of two colors. This allows the operator to take quality-control readings in a time-efficient manner without having to create tolerances or store data.

The Sphere

The SP62's diffusing sphere is made of Spectralon®, a durable, highly reflective material designed to perform in a rigorous production environment. The diffusing material prevents premature degradation due to the flaking and chipping of the sphere wall material.

Opacity, Color Strength and Shade Sorting

The SP62 can measure opacity as well as three color-strength options: chromatic, apparent and tri-stimulus calculations. The SP62 also performs 555 shade sorting. These are important considerations in the color quality control of manufactured products involving plastic, painted or textile materials.

Inter-Instrument Agreement

The SP62 has superior inter-instrument agreement—essential in multiple-instrument color-control programs. The SP62 offers excellent inter-instrument agreement with X-Rite's SP64 sphere spectrophotometer. Both input data into X-Rite's line of Windows-based color quality assurance and color formulation software.

Texture and Gloss Influence

To determine the influence of the specular component, the SP62 allows simultaneous measurement of both specular-included (color) and specular-excluded (appearance).

User-Friendly Ergonomics

In addition to on-board programs to assist the operator in the data collection process, the instrument itself is highly user-friendly. It is compact and lightweight. A wrist strap and tactile side grips make it easy to hold. Read-outs are large and easy to see. A rechargeable battery pack allows extended operation of the instrument.

SPECIFICATIONS:

MEASURING GEOMETRICS

d/8°, DRS spectral engine, choice of optical aperture:

- 4mm measurement area
6.5mm target window
- 8mm measurement area
13mm target window
- 14mm measurement area
20mm target window

LIGHT SOURCE

Gas-filled tungsten lamp

ILLUMINANT TYPES

C, D50, D65, D75, A, F2, F7, F11 & F12

STANDARD OBSERVERS

2° & 10°

RECEIVER

Blue-enhanced silicon photodiodes

SPECTRAL RANGE

400 – 700nm

SPECTRAL INTERVAL

10nm – measured
10nm – output

STORAGE

1,024 standards with tolerances,
2,000 samples

MEASUREMENT RANGE

0 to 200% reflectance

MEASURING TIME

Approx. 2 seconds

INTER-INSTRUMENT AGREEMENT

CIE L*a*b*:

Avg. 0.20 ΔE^*_{ab} based on avg.
of 12 BCRA Series II tiles
(specular component included)
Max. 0.40 ΔE^*_{ab} on any tile
(specular component included)

CMC equivalent:

Avg. 0.15 ΔE^*_{cmc} based on avg.
of 12 BCRA Series II tiles
(specular component included)
Max. 0.30 ΔE^*_{cmc} on any tile
(specular component included)

SHORT-TERM REPEATABILITY¹

.05 ΔE^*_{ab} on white ceramic
(Standard deviation)

LAMP LIFE

Approx. 500,000 measurements

POWER SUPPLY

Removable (Ni-metal hydride)
battery pack; 7.2 VDC rated
@ 1650 mAh.

AC ADAPTER REQUIREMENTS

90–130VAC or 100–240VAC,
50–60Hz, 15W max.

CHARGE TIME

Approx. 4 hours – 100% capacity

MEASUREMENTS PER CHARGE

1,000 measurements within 8-hour
period

DATA INTERFACE

Patented bi-directional RS-232,
300-57,600 baud

DISPLAY

128 x 256 pixel graphical LCD

OPERATING TEMPERATURE RANGE

50° to 104°F (10° to 40°C)
85% relative humidity maximum
(non-condensing)

STORAGE TEMPERATURE RANGE

-4° to 122°F (-20° to 50°C)

WEIGHT

2.4 lbs. (1.1 kg)

DIMENSIONS

4.3" H 3.3" W 7.7" L
(10.9 cm 8.4 cm 19.6 cm)

ACCESSORIES PROVIDED

Calibration standards, operation
manual, AC adapter, carrying case

OPTIONS

Optional remote battery charger
and replacement rechargeable bat-
tery packs available

¹Based on 20 measurements on a white tile.

* Specifications and design subject to change
without notice. X-Rite standards are traceable to
National Institute of Standards and Technology,
Gaithersburg, USA.



xrite.com

X-RITE WORLD HEADQUARTERS

Grandville, Michigan USA
(616) 534-7663
(800) 248-9748
FAX (616) 534-8960

X-RITE LATIN AMERICA

Hollywood, Florida USA
954-927-4979
FAX 954-927-4979

X-RITE LTD.

Poynton, Cheshire
United Kingdom
44 (0) 1625 871100
FAX 44 (0) 1625 871444

X-RITE MEDITERRANÉE

Massy, France
33 1-6953-6620
FAX 33 1-6953-0052

X-RITE ITALY S.R.L.

Origgio (VA), Italy
(39) 02-967-34266
FAX (39) 02-967-30681

X-RITE GmbH

Köln, Germany
(49) 2203-91450
FAX (49) 2203-914519

X-RITE INTERNATIONAL

TRADING LIMITED
Shanghai, PR China
86-21-6427-2426
FAX 86-21-6427-5816

X-RITE ASIA PACIFIC LTD.

Quarry Bay, Hong Kong
(852) 2-568-6283
FAX (852) 2-885-8610

X-RITE Ibérica

Barcelona, Spain
34 93 567 70 73
FAX 34 93 567 70 78

Vyskov, Czech Republic

(00) 420 517-320-331
FAX (00) 420 517-320-335

X-Rite K.K.

Tokyo, Japan
81-3-5439-5971
FAX 81-3-5439-5972

ISO 9001
Certified

INFORMATION PROVIDED IN THIS DOCUMENT IS PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESSED OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND/OR FITNESS FOR A PARTICULAR PURPOSE. The user assumes the entire risk as to the accuracy and the use of this information. All text must be copied without modification and all pages must be included. All components of this information must be distributed together. This information may

not be distributed for profit. © X-Rite, Incorporated 2005. X-Rite® is a registered trademark of X-Rite, Incorporated. Other brand and product names are trademarks of their respective holders. All trademarks may be registered in the United States and/or other countries. Product design and specifications subject to change without notice.